

# 9000 Portable Multifunction Calibrator

## FW Changelog

### Version 1.001

- Updated algorithm for selecting resistance standards via SOUR:RES:FIX command.
- Bug fix: Output is kept on for the entire calibration point when calibrating analog meters in Caliber program.

### Version 1.002

- Updated algorithm for selecting capacitance standards via SOUR:CAP:AMPL command.
- Safety updates: I+SEC terminal limited to 2 A, switching output on by clicking on terminal diagram can be disallowed by the user in Menu.
- User interface updates: Click on empty space removes focus from selected control, arrow key layout is now saved on power down.

### Version 1.005

- Added SCPI commands for voltage selection in frequency function.
- Minor improvements and bug fixes.